

ID	Name	Designator	Footprint	Quantity	Supplier Part
1	18650	U2,U3	18650*2-SMD	2	
2	2.2uH	L1,L2	IND-SMD_L5.4-W5.1	2	C325962
3	10uF	C9,C10	C0805	2	C15850
4	2.2uF	C14,C11	C0603	2	C106853
5	8.66K	R10	R0603	1	C23114
6	1	R14	R0603	1	C22936
7	732	R18	R0603	1	C23106
8	10K	R19,R25,R11, R15,R17,R12	R0603	6	C25804
9	300K	R22	R0603	1	C23024
10	6.2K	R23	R0603	1	C4260
11	110K	R26	R0603	1	C25805
12	SY6982EQDC	U8	QFN-16_L3.0-W3.0- P0.50-BL_SY6982EQDC	1	C108510
13	22uF	C7,C12	C1206	2	C77091
14	100pF	C8	C0603	1	C1635
15	100nF	C13,C6,C1,C2 ,C3,C4	C0603	6	C14663
16	10nF	C16	C0603	1	C115056
17	204-10SUGD	LED1	LED-TH_BD3.0-P2.54-FD	1	C99761
18	204-10UYOC	LED2	LED-TH_BD3.0-P2.54-FD	1	C99759
19	12.7K	R8	R0603	1	C22866
20	86.6K	R9	R0603	1	C23121
21	620	R16	R0603	1	C23220
22	5.1K	R20,R27	R0603	2	C23186
23	3.3K	R21	R0603_NEW	1	C22978
24	MF52	R24	RES-TH_L2.5-W2.5- P1.70-D0.3	1	C13424
25	MIC2253-06YML- TR	U7	MLF-12-L3.0-W3.0- P0.50-BL-EP	1	C128575
26	10uF	C5	C1206	1	C9807
27	470nF	C15	C0603	1	C326058
28	84.5K	R13	R0603	1	C23118
29	SS-12D28L7	SW1	SW-TH_3P-P4.00_L7.0- W18.0	1	C319006
30	SS54	D1	SMA_L4.4-W2.8-LS5.4- R-RD	1	C513478
31	TF075N03M	Q1,Q3	PDFN3333-8_L3.1-W3.2- P0.65-LS3.4-BL	2	C2839901
32	GT-USB-7037	USB1	USB-C-TH_GT-USB- 7037	1	C2762981
33	M3定位孔	H1,H2,H3,H4	3.0MM定位孔	4	
34	HX3400A	Q2,Q4	SOT-23-3_L2.9-W1.6- P1.90-LS2.8-BR	2	C296286
35	100	R1,R5	R0603	2	C22775
36	62	R2,R6	R2512	2	C44304
37	330	R3,R4	R0603	2	C23138
38	2K	R7	R0603	1	C22975
39	HY2213-BB3A	U1,U6	SOT-23-6_L2.9-W1.6- P0.95-LS2.8-BR	2	C113632
40	HY2120-LB	U4	SOT-23-6_L2.9-W1.6- P0.95-LS2.8-BR	1	C168778
41	5.0-2P	U5	CONN-TH_2P- P5.08_L8.5-W10.2	1	C395885