

No.	Quant	Comment	Designator	Footprint	Value
1	1	2700Hz	BUZZER1	BUZ-TH_BD9.0-P4.00-D0.6-FD	2700Hz
2	4	100nF	C1, C2, C4, C6	C0805	100nF
3	1	22pF	C5	C0805	22pF
4	3	4.7uF	C8, C9, C10	C0805	4.7uF
5	1	10nF	C11	C0805	10nF
6	1	B2B-XH-A (LF) (SN)	CN2	CONN-TH_B2B-XH-A-LF-SN	
7	1	FJ5461AH 红色	D1	LED-SEG-TH_FJ5461AH	
8	2	1N5819WS	D2, D3	SOD-323_L1.8-W1.3-LS2.5-RD	
9	2	PZ254V-11-04P	H1, H2	HDR-TH_4P-P2.54-V-M	
10	1	PZ254V-11-01P	H3	HDR-TH_1P-P2.54-V-M	
11	3	NCD0805R1	LED1, LED2, LED3	LED0805-RD_RED	
12	1	SS8050	Q1	SOT-23-3_L2.9-W1.3-P1.90-LS2.4-BR	
13	1	A03401	Q2	SOT-23-3_L2.9-W1.4-P1.90-LS2.6-BR	
14	10	10K	R1, R2, R4, R5, R6, R7, R9, R10, R11, R12	R0805	10K
15	1	1K	R3	R0805	1K
16	1	560	R8	R0805	560
17	2	TS-1101-C-W	RST, SW1	SW-SMD_L6.0-W3.3-LS8.0	
18	4	Key_SMD_6x6x6.5	SW2, SW3, SW4, SW5	SW-SMD_4P-L6.0-W6.0-P4.50-LS9.0-2	
19	4	M3螺丝	TP1, TP2, TP3, TP4	M3螺丝	
20	1	R7FA2E1A72DFL#AA0	U1	LQFP-48_L7.0-W7.0-P0.50-LS9.0-BL	
21	1	DHT11	U2	SENSOR-TH_DHT11	
22	1	TP4056	U3	ESOP-8_L4.9-W3.9-P1.27-LS6.0-BL-EP	
23	1	TYPE-C-31-M-33	USB1	USB-C-TH_TYPE-C-31-M-33	