

ID	Name	Designator	Footprint	Quantity	Supplier Part
1	0	R15	R0603	1	C21189
2	1uF	C34,C58	CAP-TH_L7.2-W6.0-P5.00-D0.6	2	C328852
3	220nF	C56,C57,C8,C14,C16,C21,C37,C43	C0603	8	C107083
4	47K	R17	R0603	1	C25803
5	75K	R18	R0603	1	C4184
6	TPA3118D2DAPR	U3,U2	HTSSOP-32_L11.0-W6.1-P0.65-LS8.1-BL-EP	2	C46497
7	1nF	C1,C6,C10,C18,C25,C27,C30,C35,C39,C45,C49	C0603	11	C8808
8	100nF	C2,C4,C28,C31,C33,C46,C52,C53,C5	C0603	9	C14663
9	220uF	C3,C29,C32,C47	CAP-TH_BD6.3-P2.50-D1.0-FD	4	C171433
10	680nF	C5,C13,C17,C24	CAP-TH_L7.2-W4.5-P5.00-D0.6	4	C280298
11	10nF	C7,C11,C19,C23,C36,C40	C0603	6	C327204
12	1uF	C9,C12,C15,C20,C22,C38,C41,C44	C0603	8	C59302
13	2.2uF	C26,C48	C0603	2	C309478
14	4.7uF	C50,C51	C0805	2	C98195
15	220nF	C55	C0603	1	C335532
16	XHB-2A Connector	CN1,CN2,CN4	CONN-TH_XHB-2A	3	C57981
17	10uH	L1,L2,L3,L4,L5,L6	IND-SMD_L7.0-W6.6_MCW-0650-220	6	C177256
18	3.3	R1,R3,R4,R7,R8,R12,R14,R16	R0603	8	C22979
19	100K	R2,R5,R13	R0603	3	C25803
20	20K	R6,R21,R22,R25	R0603	4	C4184
21	330K	R9,R19	R0603	2	C23137
22	470K	R10,R20	R0603	2	C23178
23	10K	R11,R23,R24	R0603	3	C25804
24	XH2.54-9A	CN3	CONN-TH_XH2.54-9A	1	C33435
25	M3定位孔	H1,H2,H3,H4	3.0MM定位孔	4	
26	33K	R26	R0603	1	C4216
27	5.1K	R27	R0603	1	C23186
28	5.0-2P	U1	CONN-TH_2P-P5.08_L8.5-W10.2	1	C395885
29	NE5532DR	U4	SOIC-8_L4.9-W3.9-P1.27-LS6.0-BL	1	C7426

